

# Precision Results and Increased Productivity for Dental Labs and Technicians

The DWX-30 is Roland's compact 4-axis CNC milling machine built on more than 20 years of experience in CNC milling technology. The DWX-30 works with zirconia and wax to create flawless dental prostheses, including crowns, bridges, abutments, bars and dental arches with perfect anatomical structure. As an open system, the DWX-30 operates with industry standard scanners and CAD/CAM software. Vacuum lines are included for dust and particle collection. Designed for quality, high-speed machining, the DWX-30 is compact, clean and quiet.



Precision milling of zirconia




Milling wax copings



Wax crowns and bridges

## High Quality Machining in Zirconia and Wax

The DWX-30 was designed to cut high quality crowns, copings and bridges in zirconia and wax. Zirconia, which can be processed only by milling, has become popular for its outstanding strength and natural look and feel, resulting in higher profit margins for dental labs and technicians. With the DWX-30, users have the ability to create precision models of consistent quality, saving time and money. A circular vise securely positions materials for the highest levels of accuracy and detail and automatically rotates for unattended production.



Materials secured in the vise

## Automated Production for Increased Productivity

The DWX-30 includes a high-performance tool length detection sensor which helps achieve precision cutting. Once installed, you simply start the detection process which measures the tool automatically. This system helps you achieve precision cutting with minimal downtime. A 4th rotary axis unit is also included with the DWX-30 and mills up to two sides automatically. Once a side is finished, the piece is automatically rotated until both sides are completed, expediting the production process.



Automatic rotary axis mills up to two sides.

## Powerful, Precision Milling Spindle

The DWX-30's standard spindle is built for stability and to withstand the vibrations of high-speed milling. The spindle's high-torque motor performs consistently regardless of the milling speed. Energy efficient, the DWX-30 can be operated from a standard power outlet without a dedicated electrical line. The DWX-30 operates at speeds from 6,000 to 30,000 RPM to support zirconia and wax materials.



Powerful spindle unit built for precision milling.

## Easy to Use and Clean for a Safe Work Space

The DWX-30 comes with both an external control panel and a virtual screen panel. Both can be used to easily control the movement of axes while the virtual panel can set up the machine, set origin points, measure tool length and more. The DWX-30's dust collection capsule captures all milling material for a clean work environment. Two hoses connect to the capsule to immediately remove dust particles and chips throughout the production process. The DWX-30's front cover is made of transparent plexiglass for a clear view of the milling process.



External Handy Panel



Dust collection capsule captures milling material, keeping the work area clean.

Specifications		DWX-30
Cuttable material		Zirconia and modeling wax
Loadable workpiece shape	Cylindrical (without levels)	External diameter: 98mm, Height: 10 – 14mm External diameter: 100mm, Height: 10 – 14mm
	Cylindrical (with levels)	External diameter (level section): 98mm, External diameter (body section): 95mm, Height: 12 – 26mm External diameter (level section): 100mm, External diameter (body section): 95mm, Height: 12 – 26mm
	Block	Width x Depth: 40 x 75mm, Height: 12 – 26mm
Loadable workpiece weight		1.4kg
X, Y, and Z operation strokes		239 x 205 x 100 mm (9.4 x 8.1 x 3.9 in.)
Maximum angle of rotation		±18×10° (±5000 rotations)
X-, Y-, and Z-axis drive system		Stepping motor
Operating speed		X and Y axes: 0.1 to 60 mm/sec. (0.004 to 2.4 in./sec.) Z axis: 0.1 to 30 mm/sec. (0.004 to 1.2 in./sec.) A axis: 11.25 rpm
Software resolution		X, Y and Z axes: 0.01mm/step (0.0004 in./step), A axis: 0.0225°
Mechanical resolution		X and Y axes: 0.00125 mm/step (0.00005in./step) (micro-step control) Z axis: 0.00125 mm/step (0.00005in./step) (micro-step control) A axis: 0.0028125° (micro-step control)
Spindle motor		Brushless DC motor, maximum 100W
Spindle rotation		6,000 to 30,000 rpm
Tool chuck		Collet method
Interface		USB (compliant with Universal Serial Bus Specification Revision 1.1)
Control command set		RML-1
Power requirements		AC 100 to 120 V±10%, 50/60 Hz (overvoltage category II, IEC 60664-1), 2.8 A AC 220 to 240 V ±10%, 50/60 Hz (overvoltage category II, IEC 60664-1), 1.2 A
Power consumption		275 W
Acoustic noise level		During operation: 60 dB (A) or less (when not cutting) During standby: 40 dB (A) or less
Dimensions		606(W) x 656(D) x 557(H) mm (23.9(D) x 25.9(H) x 22(D) in.)
Weight		47 kg (104 lb)
Environmental		Temperature: 5 to 40°C (41 to 104 °F) Humidity: 35 to 80% (no condensation) Ambient pollution degree: 2 (as specified by IEC 60664-1)
Nonconductive pollution degree		2 (as specified by IEC 60664-1)
Included items		Power cord, handy panel, collet (diameter 3.175 mm, 4.0 mm, 3.0 mm), detection pin, cap*, spacer (A, B)*, Clamp for block workpiece (C-1, C-2, D-1, D-2), User's Manual, Roland Software Package CD-ROM, etc.

\*DWX-30 will be shipped from the factory with the cap and spacer A installed on it.


System Requirements for USB Connection	
Computer	Model preinstalled with 32 or 64-bit Windows 7, Windows Vista, or Windows XP, or any later operating system
USB cable	Use the included USB cable

## Roland DG Corporation

Roland DG Corporation is a leading worldwide manufacturer of precision digital devices, including wide format inkjets, milling and engraving machines, vinyl cutters, 3D scanners, a jewelry wax model maker and photo impact printers. In addition, the company offers software and other components that provide professionals with complete solutions. With ownership, Roland DG customers get legendary Roland reliability and world-class service, support and training. Roland DG is ISO 14001:2004 and ISO 9001:2008 certified. The company strives to preserve environmental protection while maintaining the highest quality standards.



Roland DG products that feature this environmental label meet the company's criteria for environmental consciousness, a set of standards based on ISO 14021 self-declaration type II. For more information, please visit [www.rolanddg.com](http://www.rolanddg.com).



### ISO 14001:2004 and ISO 9001:2008 Certified

Roland pursues both environmental protection and continuous quality improvement. Under the philosophy of preserving the environment and human health, Roland is actively working to abolish organic solvents in production, to reduce and recycle waste, to reduce power use, and to purchase recycled products. Roland constantly strives to provide the most highly reliable products available.



Roland reserves the right to make changes in specifications, materials or accessories without notice. Your actual output may vary. For optimum output quality, periodic maintenance to critical components may be required. Please contact your Roland dealer for details. No guarantee or warranty is implied other than expressly stated. Roland shall not be liable for any incidental or consequential damages, whether foreseeable or not, caused by defects in such products. All trademarks are the property of their respective owners. Roland DG Corp. has licensed the MMP technology from the TPL Group.